

Posi-Lock Usage & Packs

We recommend the NL-series for connecting 2 wires together, such as Siren wires.
Be sure to confirm the size of your wires before purchasing.

How to Use



Connect your Alarm's Siren Output wire to the appropriate wire on your Siren.

1 Strip 10mm off your wire and insert into one removed cap.

10mm
0.5~1.0mm
18~24AWG

2 Insert cap into body with bare wire protruding. Screw tight.

Posi-Lock Conn.

Normal Siren
Connect here.
RED
BLK
+12V
Car BATTERY

Battery Backup Siren
Connect here.
BRN
RED
BLK
+12V
Car BATTERY

Posi-Lock 4-pack

NL-4

PRICE ¥ 600 + tax

CODE: 4571114022944



Posi-Lock 10-pack

NL-10

PRICE ¥ 1,300 + tax

CODE: 4571114022982



Posi-Lap 100-pack

NL-100

PRICE ¥ 12,000 + tax

CODE: 4571114022999

English documentation
will be included.

